

Light source Deuterium-halogen

Noor Imen Tajhiz Co



Deuterium tungsten light source

The spectral range of the light source is 200-1100 nm. Depending on the type of test, the user can use the ultraviolet or visible area or the entire area simultaneously as a single channel.

This product has three output ports for liquid absorption spectroscopy, reflection spectroscopy of solids, powders and thin films. It is also suitable for photoluminescence testing.

The output ports are all SMA905 connectors.

FOR MORE INFORMATION CALL:

Phone: 031-55805015

Email: info@hyperspectralimaging.ir

Mob: 09137433570, 09336806899

noorimentajhiz.co@gmail.com

Tlgram: <https://t.me/Noorimentajhiz>

Instagram: Noor_imen_tajhiz

<http://hyperspectralimaging.ir>